



Crank and Connecting Rod Apparatus (SMT-TM-01)

The crank slider, unlike a normal crank mechanism, generates a purely harmonic stroke movement. The SMT-TM-01 unit can be used to generate and study purely harmonic stroke movements. The experimental unit comprises a rotating crank disk, connecting rod and fixed cylinder. The connecting rod is connected to the crank disk on one side via a crank. Changing the position of the crank on the crank disk adjusts the crank radius in three positions. At the other end, the connecting rod is connected to the fixed cylinder. This end models the piston. The angle is adjusted using the crank disk, and an angle scale is integrated into the base plate. A millimetre- precise steel ruler is attached to the cylinder to measure the stroke.

TECHNICAL SPECIFICATIONS

Specifications:

- Investigation of a crank slider.
- Generation and investigation of purely harmonic stroke movements.
- Adjustment of the crank radius at three positions of the connecting rod on the crank disk.
- Adjustment of the angle by turning the crank disk.

Technical Data:

- Crank disk:
 - Anodised aluminium, Ball-bearing mounted.
- Crank radius:
 - 25mm, 37.5mm, 50mm.
- Connecting rod:
 - Anodised aluminium.
- Cylinder:
 - Stroke 0 to 100mm.

Experimental Data:

Crank mechanism with fixed and oscillating cylinder.



Web: http://www.esolsengineering.com, Email: esolsengineering@gmail.com (We reserve the right to modify our products without any notifications)

Page 1 of 1